

PRODUCT-DETAILS

316EP6

Industrial Plugs, 3P+E, 16A, 380 ... 415 V



General Information

Extended Product Type	316EP6
Product ID	2CMA101956R1000
EAN	7392696019569
Catalog Description	Industrial Plugs, 3P+E, 16A, 380 ... 415 V
Long Description	Industrial Plugs, 3P+E, 16A, 380 ... 415 V Clock Position Of Grounding Contact 6 hour Color code Red

Ordering

E-Number (Sweden)	E2416165
E-Number (Finland)	2420060
E-Number (Norway)	1540710
EAN	7392696019569
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	69 mm
Product Net Height	75 mm

Product Net Length	144 mm
Product Net Depth / Length	144 mm
Product Net Weight	0.16 kg

Container Information

Package Level 1 Width	138 mm
Package Level 1 Depth / Length	158 mm
Package Level 1 Height	345 mm
Package Level 1 Gross Weight	1.6 kg
Package Level 1 EAN	7392696029889
Package Level 1 Units	box 10 piece

Technical UL/CSA

Tightening Torque UL/CSA	7.1 in-lb
-----------------------------	-----------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1617364
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1 ... 2.5 mm ²
Cable Diameter	17 mm
Cable Entry Position	Swivel
Color	Red
Connection Type	Screw Clamp
Degree of Protection	IP44
Enclosure Material	Plastic (PA)
Frequency (f)	50 Hz 60 Hz
Function	Plug
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#316EP6
Material	Plastic
Number of Poles	4

Order Multiple	10 piece
Product Main Type	EP
Product Name	Industrial Plug
Protection Type	Splashproof
Rated Current (I_n)	16 A
Rated Voltage (U_r)	380 ... 415 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440509
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Plugs

