

PRODUCT-DETAILS

# 232EP4

## Industrial Plugs, 2P+E, 32A, 100 ... 130 V



### General Information

Extended Product Type	232EP4
Product ID	2CMA101974R1000
EAN	7392696019743
Catalog Description	Industrial Plugs, 2P+E, 32A, 100 ... 130 V
Long Description	Industrial Plugs, 2P+E, 32A, 100 ... 130 V Clock Position Of Grounding Contact 4 hour Color code Yellow

### Ordering

E-Number (Sweden)	E2416171
E-Number (Finland)	2420070
EAN	7392696019743
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

### Dimensions

Product Net Width	79 mm
Product Net Height	83 mm
Product Net Length	167 mm

Product Net Depth / Length	167 mm
Product Net Weight	0.21 kg

### Container Information

Package Level 1 Width	154 mm
Package Level 1 Depth / Length	182 mm
Package Level 1 Height	378 mm
Package Level 1 Gross Weight	2.1 kg
Package Level 1 EAN	7392696030069
Package Level 1 Units	box 10 piece
Package Level 2 Units	450 piece

### Technical UL/CSA

Tightening Torque UL/CSA	10.6 in-lb
-----------------------------	------------

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1617364
REACH Declaration	2CMC700005D0001

### Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 6 mm <sup>2</sup>
Cable Diameter	22 mm
Cable Entry Position	Swivel
Color	Yellow
Connection Type	Screw Clamp
Degree of Protection	IP44
Enclosure Material	Plastic (PA)
Frequency (f)	50 Hz 60 Hz
Function	Plug
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#232EP4
Material	Plastic
Number of Poles	3

Order Multiple	10 piece
Product Main Type	EP
Product Name	Industrial Plug
Protection Type	Splashproof
Rated Current ( $I_n$ )	32 A
Rated Voltage ( $U_r$ )	100 ... 130 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

---

## Classifications

eClass	27440509
UNSPSC	39120000

---

## Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

---

## Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Plugs

