

PRODUCT-DETAILS

332EP6

Industrial Plugs, 3P+E, 32A, 380 ... 415 V



General Information

| | |
|-----------------------|---|
| Extended Product Type | 332EP6 |
| Product ID | 2CMA101984R1000 |
| EAN | 7392696019842 |
| Catalog Description | Industrial Plugs, 3P+E, 32A, 380 ... 415 V |
| Long Description | Industrial Plugs, 3P+E, 32A, 380 ... 415 V Clock Position Of Grounding Contact 6 hour Color code Red |

Ordering

| | |
|------------------------|---------------------|
| E-Number (Sweden) | E2416174 |
| E-Number (Finland) | 2420079 |
| E-Number (Norway) | 1540714 |
| EAN | 7392696019842 |
| Country of Origin | Czech Republic (CZ) |
| Minimum Order Quantity | 10 piece |

Dimensions

| | |
|--------------------|-------|
| Product Net Width | 79 mm |
| Product Net Height | 83 mm |

| | |
|----------------------------|---------|
| Product Net Length | 167 mm |
| Product Net Depth / Length | 167 mm |
| Product Net Weight | 0.23 kg |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Width | 154 mm |
| Package Level 1 Depth / Length | 182 mm |
| Package Level 1 Height | 378 mm |
| Package Level 1 Gross Weight | 2.3 kg |
| Package Level 1 EAN | 7392696030168 |
| Package Level 1 Units | box 10 piece |
| Package Level 2 Units | 450 piece |

Technical UL/CSA

| | |
|-----------------------------|------------|
| Tightening Torque UL/CSA | 10.6 in-lb |
|-----------------------------|------------|

Certificates and Declarations (Document Number)

| | |
|-----------------------------------|-----------------|
| Declaration of Conformity - CE | 2CMC700005D0001 |
| Declaration | 2CMC700005D0001 |
| Environmental Information | 2CMC000056M0000 |
| RoHS Information | 2CMC700005D0001 |
| SEMKO Certificate | 1617364 |
| REACH Declaration | 2CMC700005D0001 |

Additional Information

| | |
|------------------------|---------------------------|
| Additional Information | 3P+E |
| Ambient Temperature | -25 ... 40 °C |
| Cable Cross-Section | 2.5 ... 6 mm ² |
| Cable Diameter | 22 mm |
| Cable Entry Position | Swivel |
| Color | Red |
| Connection Type | Screw Clamp |
| Degree of Protection | IP44 |
| Enclosure Material | Plastic (PA) |
| Frequency (f) | 50 Hz 60 Hz |
| Function | Plug |
| Housing Material | Plastic (PA) |
| Invoice Description | Ind. P&S#332EP6 |
| Material | Plastic |

| | |
|----------------------------|----------------------------------|
| Number of Poles | 4 |
| Order Multiple | 10 piece |
| Product Main Type | EP |
| Product Name | Industrial Plug |
| Protection Type | Splashproof |
| Rated Current (I_n) | 32 A |
| Rated Voltage (U_r) | 380 ... 415 V |
| Recommended Screw Driver | PH2 |
| Standards | IEC 60309-1, -2 |
| Suitable for Product Class | IEC Industrial Plugs and Sockets |
| Instructions and Manuals | 2CMC700014C0016 |
| RAL Number | RAL 7012 - Basalt Grey |

Classifications

| | |
|--------|----------|
| eClass | 27440509 |
| UNSPSC | 39120000 |

Technical

| | |
|-------------------|---------------|
| Wire Size | 12 ... 10 AWG |
| Tightening Torque | 1.2 N·m |

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Plugs

