

PRODUCT-DETAILS

# 332P6W

## Ind. P&S#332P6W



### General Information

Extended Product Type	332P6W
Product ID	2CMA166738R1000
EAN	7392696667388
Catalog Description	Ind. P&S#332P6W
Long Description	Plug, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

### Ordering

E-Number (Sweden)	E2416268
E-Number (Finland)	2421644
E-Number (Norway)	2416268
EAN	7392696667388
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

### Dimensions

Product Net Width	94 mm
Product Net Height	94 mm

Product Net Length	147 mm
Product Net Depth / Length	147 mm
Product Net Weight	0.3 kg

---

## Container Information

Package Level 1 Width	95 mm
Package Level 1 Depth / Length	95 mm
Package Level 1 Height	175 mm
Package Level 1 Gross Weight	0.4 kg
Package Level 1 EAN	7392696667388
Package Level 1 Units	box 1 piece
Package Level 2 Units	400 piece

---

## Technical UL/CSA

Tightening Torque UL/CSA	10.6 in-lb
-----------------------------	------------

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1025779
REACH Declaration	2CMC700005D0001

---

## Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 6 mm <sup>2</sup>
Cable Diameter	13 ... 21.5 mm
Cable Entry Position	Cable entry compression gland
Color	Red
Connection Type	Screw Clamp
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Plug
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#332P6W

Material	Plastic
Number of Poles	4
Order Multiple	1 piece
Product Main Type	TP
Product Name	Industrial Plug
Protection Type	Watertight
Rated Current ( $I_n$ )	32 A
Rated Voltage ( $U_r$ )	380 ... 415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Plugs
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700002D0001
RAL Number	RAL 7001 - Silver Grey

## Classifications

eClass	27440509
UNSPSC	39120000

## Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

## Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Plugs

