

PRODUCT-DETAILS

463P6W

Ind. P&S#463P6W



General Information

Extended Product Type	463P6W
Product ID	2CMA166798R1000
EAN	7392696667982
Catalog Description	Ind. P&S#463P6W
Long Description	Plug, earthing sleeve position 6h, rated current 63A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416294
E-Number (Finland)	2421649
E-Number (Norway)	1563683
EAN	7392696667982
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	114 mm
Product Net Height	114 mm

Product Net Length	275 mm
Product Net Depth / Length	275 mm
Product Net Weight	1.15 kg
Mechanical Drawings	9AKK107492A4181

Container Information

Package Level 1 Width	120 mm
Package Level 1 Depth / Length	138 mm
Package Level 1 Height	285 mm
Package Level 1 Gross Weight	1.24 kg
Package Level 1 EAN	7392696667982
Package Level 1 Units	box 1 piece
Package Level 2 Units	120 piece

Technical UL/CSA

Tightening Torque UL/CSA	31 in·lb
-----------------------------	----------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1025779
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	4 ... 16 mm ²
Cable Diameter	17 ... 35 mm
Cable Entry Position	Cable entry, compression gland, internal and external cable clamp
Color	Red
Connection Type	Screw Clamp
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Plug
Housing Material	Thermoplastic (PBT)

Invoice Description	Ind. P&S#463P6W
Material	Plastic
Number of Poles	5
Order Multiple	1 piece
Product Main Type	TP
Product Name	Industrial Plug
Protection Type	Watertight
Rated Current (I_n)	63 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Plugs
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000040M0001
Installation Manual	2CMC000040M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440509
UNSPSC	39121402

Technical

Wire Size	8 ... 4 AWG
Tightening Torque	3.5 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Plugs

