


Prototyping Board



RE323-LF

- EPOXY fibre-glass FR4 1.5 mm single-sided 35 µm CU
- hot air leveling (HAL-leadfree)
- 32 x 55 single-hole conductor 2.2 mm Ø
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- connector 32-channel /D DIN 41612
- connector 48-channel /E DIN 41612
- connector 48-channel /F DIN 41612
- size 100 x 160 mm