

USB-C to DVI Adapter with USB-A Port and PD Charging, Black

MODEL NUMBER: U444-06N-DUB-C



USB Type-C to DVI adapter adds DVI, USB-A and USB-C PD charging ports to your tablet, laptop, smartphone or PC.

Features

Mini Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport Workstation This USB Type-C to DVI adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting video to a large display, adding a thumb drive or other USB peripheral, and powering and charging a PD Charging-compliant mobile device—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Video DisplayPort and USB Signals With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a DVI Display To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

Connects a USB Peripheral The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with USB 2.0 and USB 1.1 devices. This dedicated BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices.

Charges a Connected Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U444-06N-DGUB-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB-C and Thunderbolt 3 to DVI adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U444-06N-DUB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a DVI display
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

- Source device with USB-C or



Thunderbolt 3 port that supports
USB DisplayPort Alternate
Mode

- Display device with DVI input
(DVI port)

Package Includes

- U444-06N-DUB-C USB-C to
DVI Adapter with USB-A Hub,
Thunderbolt 3—1080p, PD
Charging, Black, 6 in.
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332209139
OUTPUT	
Charging Ports / Amps	1.5A; 3A
Charging Watts	60
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC and ABS
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	0.50
Unit Dimensions (hwd / in.)	0.57 x 3.1 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.08
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	4.1 BTU/Hr
Power Consumption (Watts)	1.2
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C)
CONNECTIONS	
Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	DVI: 1920 X 1080 (1080P) @ 60HZ
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	Yes
Technology	USB; USB 3.1 (Gen 1); DVI; PD Charging
USB Power Delivery (PD) Charging Specification	2.0
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>