

## PoE to USB Micro-B and RJ45 Active Splitter - 802.af, 48V to 5V 1A, Up to 328 ft. (100 m)

MODEL NUMBER: NPOE-SPL-G-5VMU



Active PoE splitter separates 5V 1A power to a USB Micro-B plug and 10/100/1000 Mbps Gigabit Ethernet data to an RJ45 plug.

### Features

#### Split Your PoE Signal into Separate Power and Ethernet Connections for Edge Networks

Connect the NPOE-SPL-G-5VMU PoE (Power over Ethernet) splitter to your edge network up to 328 feet (100 meters) from a PoE switch or 48V injector. The splitter separates the power and data signals, delivering 5V 1A (5W) of power to the USB Micro-B plug and 10/100/1000 Mbps to the RJ45 data plug. This allows you more flexibility in placing devices in areas where an AC outlet is unavailable and too expensive or impractical to install.

#### Supports Power over Ethernet to Save You Money and Give You More Installation Choices

This PoE splitter supplies the power (through its USB connector) to operate non-PoE equipment, such as security cameras, VoIP telephones and wireless access points (WAP). This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. It also helps you install devices in areas far away from AC outlets, such as poles or ceilings. The NPOE-SPL-G-5VMU supports a wide range of input voltages from 36VDC to 57VDC and has a fixed USB output of 5VDC.

#### Simple Plug-and-Play Installation Has the Splitter Connected in Minutes

No configuration or software is required to add the NPOE-SPL-G-5VMU to your LAN. It complies with 802.3af (PoE), 802.3 (Ethernet), 802.3u (Fast Ethernet) and 802.3ab (Gigabit Ethernet) standards.

### Highlights

- Delivers power and data via Cat5e/6 cable up to 328 ft. to edge network equipment
- Extends 5VDC power to any network device installed where no AC outlet is available
- Supports Gigabit Ethernet data transfer speeds up to 1000 Mbps (1 Gbps)
- Designed for PoE devices like Wireless Access Points and security cameras
- Quick and easy plug-and-play installation with no configuration necessary

### Applications

- Install an Alexa-enabled device or VoIP phone in an area without a standard power connection
- Fill in Wi-Fi dead spots in your office with a wireless access point connected to your LAN
- Set up digital signage in a mall, arena, office building or theater
- Connect security cameras and other A/V surveillance equipment in a video wall

### System Requirements

- IEEE 802.3af/at-compliant PoE injector or switch
- Existing or newly installed Cat5e/6/6a cabling
- A network device with a 5V 1a USB Micro-B power port



#### Package Includes

- NPOE-SPL-G-5VMU PoE to USB Micro-B and RJ45 Active Splitter
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332242143
OUTPUT	
Output (Watts)	5W (5V/1A)
PHYSICAL	
Color	Black
Unit Dimensions (hwd / in.)	0.92 x 3.18 x 1.11
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3ab; 802.3af; 802.3u
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (MALE)
Side B - Connector 2	MICRO-USB B (MALE)
FEATURES & SPECIFICATIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	Cat5/5e; Cat6; PoE
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>