


T30LL**111-03500**

T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

Base Data**Application Method**

Quick, simple fixing by hand or with HellermannTyton tensioning tools

Colour

Black (BK)

Label E-Number Norway

13 447 84

Package Content

100

Quantity per

Bag

Recommended Application Tool

MK3SP, MK3PNSP2, MK7P, MK7, MK20

Logistic and Packaging**EAN code**

4031026259697

Quantity of Europallet

126000

Weight (kg) (Metric)

1.39 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

Product Dimensions**Bundle Diameter max (Metric)**

80

Bundle Diameter min (Metric)

1.5

Length L (Metric)

290

Minimum Tensile Strength (N)

135

Width W (Metric)

3.5