

GS2AH210

External rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, IP65, for GS 32-63A IEC



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys GS GS1D TeSys GS GS2F TeSys GS GS2G FuPact GS GSB32 FuPact GS GSC50
Type of operating handle	External right side
Handle colour	Black
Handle front plate colour	Grey

Complementary

Handle positions	O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	32 A 50 A 63 A
Standards	IEC
Net weight	0.2 kg

Environment

IP degree of protection	IP65
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------