

# GS2AH230

External rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, IP65, for GS 100-400A IEC



## Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys GS GS2J TeSys GS GS2K TeSys GS GS2L TeSys GS GS2N TeSys GS GS2P TeSys GS GS2Q FuPact GS GSB100 FuPact GS GSC125 FuPact GS GSD125 FuPact GS GSB160 FuPact GS GSB200 FuPact GS GSB250 FuPact GS GSD250 FuPact GS GSB400 FuPact GS GSD400
Type of operating handle	External right side
Handle colour	Black
Handle front plate colour	Grey

## Complementary

Handle positions	O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	100 A 125 A 160 A 200 A 250 A 315 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

	400 A
Standards	IEC
Net weight	0.24 kg

## Environment

IP degree of protection	IP65
-------------------------	------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------