

# GS2AH260

External rotary handle, TeSys GS, red handle, right side mounting, 2 positions I-O, IP65, for GS 630-1250A IEC



## Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys GS GS2S TeSys GS GS2T TeSys GS GS2V FuPact GS GSB630 FuPact GS GSD630 FuPact GS GSB800 FuPact GS GSD800 FuPact GS GSB1250 FuPact GS GSD1250
Type of operating handle	External right side
Handle colour	Red
Handle front plate colour	Yellow

## Complementary

Handle positions	O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	630 A 800 A 1250 A
Standards	IEC
Net weight	0.28 kg

## Environment

IP degree of protection	IP65
-------------------------	------

**Offer Sustainability**

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

**Contractual warranty**

Warranty	18 months
----------	-----------