

GS2AHT540

External rotary handle, TeSys GS, red handle, front mounting, 3 positions Test-I-O, IP65, for GS 100-400A IEC



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys GS GS2J TeSys GS GS2K TeSys GS GS2L TeSys GS GS2N TeSys GS GS2P TeSys GS GS2Q FuPact GS GSB100 FuPact GS GSC125 FuPact GS GSD125 FuPact GS GSB160 FuPact GS GSB200 FuPact GS GSB250 FuPact GS GSD250 FuPact GS GSB400 FuPact GS GSD400
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	Test-O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	100 A 125 A 160 A 200 A 250 A 315 A

	400 A
Standards	IEC
Net weight	0.24 kg

Environment

IP degree of protection	IP65
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------