



PRODUCT-DETAILS

EPB TEB 400 S

EPBTEB400S Protecta Top extension box, 2Row, 400mm height, steel flap

General Information

Extended Product Type	EPB TEB 400 S
Product ID	1SKA124142C0001
EAN	6221115041489
Catalog Description	EPBTEB400S Protecta Top extension box, 2Row, 400mm height, steel flap
Long Description	EPBTEB400S Protecta Top extension box, 2Row, 400mm height, steel flap

Ordering

EAN	6221115041489
Minimum Order Quantity	1 piece
Customs Tariff Number	85389132

Dimensions

Product Net Width	400 mm
Product Net Height	400 mm
Product Net Depth / Length	125 mm

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	400 mm
Package Level 1 Height	400 mm
Package Level 1 Depth / Length	125 mm
Package Level 1 Gross Weight	6 kg

Additional Information

Color	Grey
Cover Plate Type	Door
Degree of Protection	IP41
Housing Material	Steel
Interior Depth	129 mm
Mounting Type	Surface mounted (plaster)

Product Main Type	EPB_C
Product Name	Protecta top extension box
Protection Class	Isolated
Surface Finishing	Powder coating

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SKC802015C0205
Declaration of Conformity - CE	No declaration needed
Instructions and Manuals	1SKC802015C0202

Classifications

ETIM 6	EC000058 - Empty cabinet
ETIM 7	EC000058 - Empty cabinet
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Enclosures → Sub Distribution Boards → MCB Boards