

PRODUCT-DETAILS

EPB25-324 CUK

EPB25-324CUK

General Information

Extended Product Type	EPB25-324 CUK
Product ID	1SKP824142C0059
EAN	6221115055882
Catalog Description	EPB25-324CUK
Long Description	3 -phase protecta busbar type 24 way, surface, 250A, including Isolator kit EPB KIT 8C

Ordering

EAN	6221115055882
Minimum Order Quantity	1 piece
Customs Tariff Number	85389790

Dimensions

Product Net Width	400 mm
Product Net Height	1140 mm
Product Net Depth / Length	132 mm

Additional Information

Color	Grey
Cover Plate Type	Door
Degree of Protection	IP41
Housing Material	Steel
Mounting Type	Surface mounted (plaster)
Product Name	Sub Distribution
Protection Class	Grounded
Rated Current (I_n)	250 A
Surface Finishing	Powder coating

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SKC802015C0203
Declaration of Conformity - CE	1SKC100819C0001

Instructions and
Manuals

1SKC802015C0203

Classifications

ETIM 6	EC000058 - Empty cabinet
ETIM 7	EC000058 - Empty cabinet
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Enclosures → Sub Distribution Boards → Sub Distribution Boards