

PRODUCT-DETAILS

E215-16-11E

E215-16-11E Pushbutton



General Information

Extended Product Type	E215-16-11E
Product ID	2CCA703153R0001
EAN	7612270938841
Catalog Description	E215-16-11E Pushbutton
Long Description	Pushbutton 1 NO + 1 NC, Rated current: 16A/250 VACPDC, Button colour: yellow, Module width 0,5

Ordering

E-Number (Sweden)	2102804
E-Number (Switzerland)	467560078
EAN	7612270938841
Minimum Order Quantity	10 piece
Customs Tariff Number	85365000

Dimensions

Product Net Width	9 mm
Product Net Height	85 mm
Product Net Length	93 mm
Product Net Depth / Length	67.5 mm
Product Net Weight	49 g

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	96 mm
Package Level 1 Height	76 mm
Package Level 1 Depth / Length	95 mm
Package Level 1 Gross Weight	46 g
Package Level 1 EAN	7612270938841

Environmental

RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
-------------	---

Additional Information

Color	Yellow
Degree of Protection	IP20
Number of Auxiliary Contacts CO (SPDT)	0
Number of Poles	2
Number of Main Contacts NC	1
Number of Main Contacts NO	1
Options Provided	1 NO + 1 NC
Power Loss	0.5 W
Product Main Type	E215
Product Name	Pushbutton
Rated Current (I_n)	16 A
Rated Voltage (U_r)	Lamp 48 ... 48 V
Rated Operational Voltage	250 V
RoHS Date	20170426
Standards	EN60669-1

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CCC441003C0101
Declaration of Conformity - CE	2CCC441002D0601
Environmental Information	2CCC441003C0201
Instructions and Manuals	2CCC441001C0201
RoHS Information	2CCC413008D0206

Classifications

ETIM 4	EC001546 - Push button for distribution board
ETIM 5	EC001546 - Push button for distribution board
ETIM 6	EC001546 - Push button for distribution board
ETIM 7	EC001546 - Push button for distribution board
Object Classification Code	S

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Command and Signalling devices → Control Switches, Pushbuttons and Indicator Lights

