

PRODUCT-DETAILS

232RAU6

Socket-outlet, panel mounting, 6h, 32A, IP44, unified flange, angled, 2P+E



General Information

Extended Product Type	232RAU6
Product ID	2CMA193266R1000
EAN	7392696932660
Catalog Description	Socket-outlet, panel mounting, 6h, 32A, IP44, unified flange, angled, 2P+E
Long Description	Panel mounted socket, earthing sleeve position 6h, rated current 32A, IP44 splashproof, unified flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue

Ordering

E-Number (Sweden)	E2416663
E-Number (Finland)	2421272
E-Number (Norway)	1547432
EAN	7392696932660
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	110 mm
Product Net Height	114 mm

Product Net Length	114 mm
Product Net Depth / Length	114 mm
Product Net Weight	0.24 kg

Container Information

Package Level 1 Width	188 mm
Package Level 1 Depth / Length	175 mm
Package Level 1 Height	428 mm
Package Level 1 Gross Weight	2.4 kg
Package Level 1 EAN	7392696662666
Package Level 1 Units	box 10 piece
Package Level 2 Units	240 piece

Technical UL/CSA

Ampere Rating UL/CSA	32 A
Tightening Torque UL/CSA	10.6 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm ²
Cable Diameter	13 ... 21.5 mm
Color	Blue
Connection Type	Screw
Degree of Protection	IP44
Enclosure Material	Thermoplastic
Frequency (f)	50 Hz 60 Hz
Function	Panel mounted socket
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#232RAU6
Material	Plastic

Mounting Holes	85x85
Mounting Type	Unified angled flange
Number of Poles	3
Order Multiple	10 piece
Product Main Type	ERAU
Product Name	Panel mounted socket
Protection Type	Splashproof
Rated Current (I_n)	32 A
Rated Frequency (f)	50...60 Hz
Rated Voltage (U_r)	200 ... 250 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Socket Outlets for Panel Mounting
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC00058M0001
Installation Manual	2CMC00058M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440504
UNSPSC	39121406

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Socket Outlets for Panel Mounting

