

PRODUCT-DETAILS

F202 AC-40/0,1

F202 AC-40/0,1 Residual Current Circuit Breaker



General Information

| | |
|-----------------------|--|
| Extended Product Type | F202 AC-40/0,1 |
| Product ID | 2CSF202001R2400 |
| EAN | 8012542780403 |
| Catalog Description | F202 AC-40/0,1 Residual Current Circuit Breaker |
| Long Description | The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. |

Technical

| | |
|--------------------------|--|
| Standards | IEC/EN 61008 UL 1053 |
| Operating Characteristic | Instantaneous |
| Type of Residual Current | AC type |
| Rated Residual Current | 100 mA |
| Rated Current (I_n) | 40 A |
| Number of Poles | 2 |
| Power Loss | at Rated Operating Conditions per Pole 2.4 W |
| Rated Voltage (U_r) | 230/400 V |
| Rated Frequency (f) | 50...60 Hz |

Environmental

| | |
|-------------|-----------------------|
| Ambient Air | Operation -25...55 °C |
|-------------|-----------------------|

Temperature

RoHS Status

Following EU Directive 2011/65/EU

Technical UL/CSA

| | |
|-------------------------------------|----------|
| Maximum Operating Voltage UL/CSA | 277 V AC |
| Short-Circuit Current Rating (SCCR) | 0.3 mA |

Dimensions

| | |
|----------------------------|----------|
| Product Net Width | 0.035 m |
| Product Net Height | 0.085 m |
| Product Net Depth / Length | 0.069 m |
| Product Net Weight | 0.200 kg |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 0.041 m |
| Package Level 1 Height | 0.078 m |
| Package Level 1 Depth / Length | 0.096 m |
| Package Level 1 Gross Weight | 0.225 kg |
| Package Level 1 EAN | 8012542780403 |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85363030 |

Certificates and Declarations (Document Number)

| | |
|--------------------------------|-----------------------------|
| Declaration of Conformity - CE | 9AKK106713A5602 |
| Environmental Information | Refer to RoHS |
| Instructions and Manuals | Manual sheet inside the box |
| RoHS Information | 2CSC423001K2702 |

Popular Downloads

| | |
|-----------------------------------|-----------------------------|
| Data Sheet, Technical Information | 9AKK107046A0424 |
| Instructions and Manuals | Manual sheet inside the box |

Classifications

| | |
|----------------------------|--|
| Object Classification Code | Q |
| ETIM 4 | EC000003 - Residual current circuit breaker (RCCB) |

| | |
|--------|--|
| ETIM 5 | EC000003 - Residual current circuit breaker (RCCB) |
| ETIM 6 | EC000003 - Residual current circuit breaker (RCCB) |
| ETIM 7 | EC000003 - Residual current circuit breaker (RCCB) |

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

