

REZ200**115-40200**

The REZ ties have a one-hand, simple, release mechanism.



The unique, patented head design enables simple and rapid use. The tie can be inserted in the normal way and pulled tight or the tail can be twisted into the head and locked into place. The quick-release mechanism can be released by one hand - even when the tie is under tension - and is achieved by simply pinching the ears.

These releasable and reusable ties are ideal for temporary installations or the addition and/or removal of cables. Suitable for a multitude of uses, such as the packaging industry as a bag closure where access to part of the bag contents may be needed but the bag needs to be re-sealed (example - milk powder in the catering industry).

Base Data**Colour**

Black (BK)

Package Content

100

Quantity (Sold Unit / EDP)

100

Quantity per

Bag

Short Description

7.88", 50 lb., pinch release cable tie, black, 100/bag

Logisitic and Packaging**Carton Quantity**

3000

EAN code

4031026195810

Quantity of Europallet

54000

UPC

08930620753

Weight (kg) (Metric)

1.76 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

ROHS Conformity

TRUE

Product Dimensions**Bundle Diameter max (Imperial)**

1.97 "

Bundle Diameter max (Metric)

50 mm

Bundle Diameter min (Imperial)

.63 "

Bundle Diameter min (Metric)

16 mm

Length L (Imperial)

7.88 "

Length L (Metric)

200 mm

Minimum Tensile Strength (imperial)

30

Minimum Tensile Strength (N)

135 N

Width W (Imperial)

.19 "

Width W (Metric)

4.7

© HellermannTyton 2006