

**REZ300****115-40300**

The REZ ties have a one-hand, simple, release mechanism.



The unique, patented head design enables quick and simple use. The tie can be inserted in the normal way and pulled tight or the tail can be twisted into the open part of the head and locked into place. The quick-release mechanism can be released by one hand - even when the tie is under tension - by simply pinching the ears.

These releasable and reusable ties are ideal for temporary installations or the addition and/or removal of cables. Suitable for a multitude of uses, such as the packaging industry as a bag closure where access to part of the bag contents may be needed but the bag needs to be re-sealed (example - milk powder in the catering industry).

**Base Data****Colour**

Black (BK)

**Package Content**

100

**Quantity (Sold Unit / EDP)**

100

**Short Description**

12.0", 50 lb., pinch release cable tie, black, 100/bag

**Logistic and Packaging****Carton Quantity**

3500

**EAN code**

4031026195827

**Quantity of Europallet**

63000

**UPC**

08930620754

**Weight (kg) (Metric)**

2.29 kg

**Material and Specifications****Flammability**

UL94 V2

**Material Shortcut**

PA66

**Operating Temperature (Metric)**

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

**ROHS Conformity**

TRUE

**Product Dimensions****Bundle Diameter max (Imperial)**

3.15 "

**Bundle Diameter max (Metric)**

80 mm

**Bundle Diameter min (Imperial)**

.63 "

**Bundle Diameter min (Metric)**

16 mm

**Length L (Imperial)**

12.00 "

**Length L (Metric)**

305 mm

**Minimum Tensile Strength (imperial)**

30

**Minimum Tensile Strength (N)**

135 N

**Width W (Imperial)**

.19 "

**Width W (Metric)**

4.7

© HellermannTyton 2006