

T18RSF

A wide range of arrowhead fixing ties which are suitable for panel thicknesses of 0.5mm to 4.5mm and hole diameters of 4.4mm to 8.0mm.

**111-85519**

The arrowhead design, in conjunction with the supporting 'legs', ensures a firm and secure fixing. The 'legs' take up any variation in panel thickness enabling one part to suit many applications. Both the RT and FBS versions are releasable and reusable, with the FBS type having the added feature of a ladder type strap as opposed to the conventional serrated strap - this ladder type strap has the benefit of being very flexible.

For the bundling and fixing of cable harnesses, pipes & hoses in the automotive, aerospace, white goods industries and panel building.

Base Data**Colour**

Natural (NA)

Package Content

100

Quantity (Sold Unit / EDP)

100

Recommended Application Tool

MK20, MK3PNSP2, MK3SP, MK7P, MK7

Logisitic and Packaging**Carton Quantity**

8000

EAN code

4031026107356

Quantity of Europallet

144000

Weight (kg) (Metric)

0.3 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

ROHS Conformity

TRUE

Product Dimensions**Bundle Diameter max (Metric)**

16

Bundle Diameter min (Metric)

1.5

Disc Diameter (Metric)

18.5

Hole

4.65-4.85

Length L (Metric)

100

Minimum Tensile Strength (N)

80

Panel Thickness max.

3.0

Panel Thickness min.

1.0

Width W (Metric)

2.5

© HellermannTyton 2006