

REL140**131-21419**

The specially designed unique release mechanism makes this releasable and reusable tie one of the easiest to operate, it can be quickly and simply opened with one hand.

Ideal for use where there is the need to repeatedly open and close the tie - both industrial and commercial applications, for example: bundling garden hoses, extension cables, harness manufacture.

The REL series have a simple opening mechanism.

**Base Data****Colour**

Natural (NA)

Label E-Number Norway

13 447 30

Package Content

100

Quantity (Sold Unit / EDP)

100

Logistic and Packaging**Carton Quantity**

4000

EAN code

4031026115337

Quantity of Europallet

72000

Weight (kg) (Metric)

2.2 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

ROHS Conformity

TRUE

Specification

UL

Product Dimensions**Bundle Diameter max (Metric)**

35

Bundle Diameter min (Metric)

6

Length L (Metric)

140

Minimum Tensile Strength (N)

200

Width W (Metric)

7.5

© HellermannTyton 2006