

Plug connector NPQH-D-Q12-E-P10

Part number: 578327

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal width | 11 mm |
| Type code | NPQH |
| Mounting position | Any |
| Pack size | 10 |
| Design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar ... 20 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| For use in the food industry | See supplementary material information |
| Ambient temperature | 0 °C ... 150 °C |
| Product weight | 37 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 12 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 12 mm |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated |
| Releasing ring material | Brass, nickel-plated |
| Material of tubing seal | FPM |
| Material of tube retaining claw | High-alloy stainless steel |