

Push-in fitting NPQH-D-G38-S10-P10

Part number: 578367

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	8 mm
Type code	NPQH
Type of seal on screwed trunnion	Sealing ring
Mounting position	Any
Pack size	10
Design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	0 °C ... 150 °C
Max. tightening torque	25 Nm
Product weight	22.5 g
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	Push-in sleeve QS-10
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Material of threaded seal	FPM
Releasing ring material	Brass, nickel-plated