


Push-in T-connector NPQH-T-Q8-Q6-P10

Part number: 578387

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	5 mm
Type code	NPQH
Mounting position	Any
Pack size	10
Design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	0 °C ... 150 °C
Product weight	27.9 g
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Releasing ring material	Brass, nickel-plated
Material of tubing seal	FPM
Material of tube retaining claw	High-alloy stainless steel