



### Main

Range	TeSys
Device short name	GAC0
Product or component type	Auxiliary contact block
Product compatibility	TeSys GC TeSys GY
Mounting location	Right side
Pole contact composition	1 C/O
[Ue] rated operational voltage	250 V
[Ith] conventional free air thermal current	5 A (at 50 °C)

### Complementary

[Ui] rated insulation voltage	500 V conforming to IEC 60947-5 500 V conforming to VDE 0110
Mechanical durability	1 Mcycles
Connections - terminals	Screw clamp terminals 2.5 mm <sup>2</sup> solid Screw clamp terminals 2.5 mm <sup>2</sup> flexible
Tightening torque	0.8 N.m - on screw clamp terminals
Height	81 mm
Width	8.75 mm
Depth	60 mm
Net weight	0.016 kg

### Environment

Standards	IEC 60947-5
Product certifications	OVE CEBEC VDE NF-USE
IP degree of protection	IP20 conforming to VDE 0106

Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m without

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------