



Main

Range	TeSys
Product name	TeSys LS1
Product or component type	Fuse-disconnector
Device short name	LS1D
Poles description	3P

Complementary

Mounting support	Rail
Mounting position	Vertical +/- 23°)
Control type	Toggle
[Ue] rated operational voltage	600 V
[Ie] rated operational current	25 A power circuit
Local signalling	Blown fuse indication
Fuse size	10 x 38 mm
Fuse type	GG AM
Associated fuse rating	30 A aM 30 A gG
Connections - terminals	spring terminals 2 0.00...0.01 in ² (1...6 mm ²)solid spring terminals 2 0.00...0.01 in ² (1...6 mm ²)flexible without cable end spring terminals 2 0.00...0.01 in ² (1...4 mm ²)flexible with cable end

Environment

Standards	IEC 60947-2 IEC 60947-4-1 IEC 60947-1
Product certifications	UR BV

IP degree of protection	IP20
Protective treatment	TH
Ambient air temperature for operation	-58...158 °F (-50...70 °C) operation
Height	3.50 in (89 mm)
Width	1.77 in (45 mm)
Depth	2.69 in (68.3 mm)
Net weight	0.60 lb(US) (0.27 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901046998
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------