

# Blanking plug QSC-16H

Part number: 153272

FESTO



## Data sheet

Feature	Value
Size	Standard
Maritime classification	See certificate
Type code	QSC
Mounting position	Any
Pack size	1
Operating pressure for entire temperature range	-0.95 bar ... 6 bar
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Product weight	4 g
Pneumatic connection 1	Push-in sleeve QS-16
Note on materials	RoHS-compliant
Housing material	PBT