

Blanking plug NPQH-P-S6-P10

Part number: 578258

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Type code | NPQH |
| Mounting position | Any |
| Pack size | 10 |
| Operating pressure for entire temperature range | -0.95 bar ... 20 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| For use in the food industry | See supplementary material information |
| Ambient temperature | 0 °C ... 150 °C |
| Product weight | 3.9 g |
| Pneumatic connection 1 | Push-in sleeve QS-6 |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated |