

Quick coupling plug NPHS-S6-M-G14

Part number: 8059258

FESTO



Data sheet

Feature	Value
Nominal width	7.85 mm
Type code	NPHS
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	20 g
Pneumatic connection 1	External thread G1/4
Note on materials	RoHS-compliant