

PRODUCT-DETAILS

EXQA0404

EXE LT STR 20MM FTNG N/P BR 1/2IN



Product image
not available

General Information

Extended Product Type	EXQA0404
Product ID	7TCA297120R0176
EAN	5011949002661
Catalog Description	EXE LT STR 20MM FTNG N/P BR 1/2IN
Long Description	Connector for Liquid Tight Conduit, Straight, Conduit Size 1/2 Inch/20mm, Thread Size 1/2 Inch NPT, For Use in Industrial and Zone 2 Applications, IP66-67 Rating, Nickel Plated Brass

Ordering

EAN	5011949002661
Customs Tariff Number	7412200035

Dimensions

Product Net Weight	.13 lb 58.957 g
--------------------	--------------------

Container Information

Package Level 1 Units	2 piece
Package Level 2 Units	10 piece
Package Level 2 Width	14 in

	356 mm
Package Level 2 Height	6 in
	152 mm
Package Level 2 Depth / Length	14 in
	356 mm

Additional Information

Application	For Use in Industrial and Zone 2 Applications to Connect Conduit Systems
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Straight Connector for Liquid Tight Conduit
Size	Conduit Size 20mm ; 1/2 Inch NPT Thread
Standards	BS EN 61386
Surface Finishing	Nickel Plated
Temperature Range	-50 to 130 °C
UPC	786210288468

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXQA0404
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXQA0404

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available