

PRODUCT-DETAILS

# EXLB0620

## Ex e Liquid tight conduit



Product image  
not available

### General Information

Extended Product Type	EXLB0620
Product ID	7TCA297120R0492
EAN	5011949246072
Catalog Description	Ex e Liquid tight conduit
Long Description	Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 32mm, Minimum Bore 26.4mm, Reel Length 20 Meters, Galvanised Steel Core with Flame Retardant PVC Covering, Black

### Ordering

EAN	5011949246072
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	.1 lb 45.351 g
--------------------	-------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	24 in 610 mm

Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	24 in 610 mm

### Additional Information

Application	Connection for Conduit Systems when Oil and Acid Resistance is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	26.4 mm
Material	Galvanized Steel Core with Flame Retardant PVC Covering
Nominal Size	32 mm
Number of Batteries	0
Product Name	LIQUID TIGHT CONDUIT
Product Type	Liquid Tight Metallic Conduit
Special Functions	Flame Retardant PVC Covering
Standards	IEC 61386
UPC	786210290195

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLB0620
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLB0620

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available