

Coaxial Cable Connector 16_716-50-7-10/003_-

Description

Right angle cable plug

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.1026 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Brass	Silver Plating

Related Documents

Outline drawing	DOU-00006865
Catalogue drawing	DOU-00006867
Assembly instruction	DOC-0000180803

Ordering Information

Single package	16_716-50-7-10/003_-E
----------------	-----------------------

Additional Information

Suitable cables	RG_214_/U, GX_07272_D, RG_393_/U, RADOX_RF_214
-----------------	--