Data Sheet

Coaxial Cable Connector 11_H4-50-4-1/133_N

Description

Straight cable plug

Interface standards



HUBER+SUHNER

Technical Data

Electrical Data		
Impedance	50 Ω	
Interface frequency max.	0.3 GHz	
Mechanical Data		
Centre contact	soldered	
Outer contact	clamped	
Weight	0.0219 kg	
Environmental Data		
Operating temperature	-65 °C to 165 °C	
2011/65/EU (RoHS - including	compliant	
2015/863 and 2017/2102)		
Material Data		
Piece Parts	Material	Surface Disting
Pièce Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Related Documents		
	DOLL 00074000	
Outline drawing Catalogue drawing	DOU-00071828 DOU-00005810	
Assembly instruction	DOC-0000179536	
Assembly instruction	DOC-0000173330	
Ordering Information		

Single package

11_H4-50-4-1/133_NE

Additional Information

Suitable cables

RG_59_B/U, GX_04273

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.