

Coaxial Cable Connector 16_MM CX-50-2-13/111_O

Description

Right angle cable plug

Interface standards

SUHNER-MM CX

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00048327
Catalogue drawing DCA-00091046
Assembly instruction DOC-0000214734

Ordering Information

Bulk 100 pcs package 16_MM CX-50-2-13/111_OH
Single package 16_MM CX-50-2-13/111_OE

Additional Information

Suitable cables SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86