Data Sheet



Coaxial Cable Connector 11_SMA-50-2-112/133_N

Description

Straight cable plug

Interface standards
IEC 60169-15 MIL-STD-348A/310 CECC 22110



2.5 to 5 GHz

26 dB

Technical Data

Electrical Data

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0026 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-65 °C to 165 °C compliant

Material Data

	OPRO / Gold Plating
O to control	
Outer contact Brass SUCC	OPLATE (R) Plating
Body Brass SUCC	OPLATE (R) Plating
Insulator PFA / PTFE	
Coupling nut Brass SUCC	OPLATE (R) Plating
Gasket VMQ (Silicone rubber)	
Crimp ferrule Copper SUCC	OPLATE (R) Plating

1 to 2.5 GHz

29 dB

Related Documents

Outline drawing DOU-00168063
Assembly instruction DOC-0000347891

Ordering Information

Bulk 500 pcs package 11_SMA-50-2-112/133_NP Single package 11_SMA-50-2-112/133_NE

Additional Information

Suitable cables ENVIROFLEX_316_D, G_02232_D, K_02252_D

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.