

Coaxial Cable Connector 16_SMA-50-4-55/199_N

Description

Right angle cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact plugged
Outer contact crimped
Weight 0.0093 kg

Environmental Data

Operating temperature -65 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|-----------------|--------------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Stainless Steel | |
| Body | Stainless Steel | |
| Other body part | Stainless Steel | |
| Insulator | PTFE (Polytetrafluoroethylene) | |
| Coupling nut | Stainless Steel | |
| Gasket | VMQ (Silicone rubber) | |
| Crimp ferrule | Copper | SUCOPLATE (R) / SUCOPRO Plating |

Related Documents

Outline drawing DOU-00007764
Assembly instruction DOC-0000201296

Ordering Information

Single package 16_SMA-50-4-55/199_NE

Additional Information

Suitable cables S_04212_B