

## Coaxial Cable Connector 11\_TNC-50-3-5/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0196 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00006494
Catalogue drawing	DOU-00006059
Assembly instruction	DOC-0000179064

### Ordering Information

Single package	11_TNC-50-3-5/133_NE
Bulk 100 pcs package	11_TNC-50-3-5/133_NH

### Additional Information

Suitable cables	RG_58_C/U, RG_223_/U, ENVIROFLEX_142, RG_400_/U
-----------------	---