

AD	REV. DIM'S/ADD NOTES
AC1	REINSTATE P/N
AC	OBSOLETE P/N
AB	REVISED
AA1	REVISED
AA	PER ECN UG1402
Z	X-RELEASE -P4
Y2	OBS. -R2 VER'S.
Y1	ADD -P4 VERSION
Y	REVISED PER
X	REVISE PER
W	REVISE PER
V	ADD -P3YW OPTION
T	ADD DYED OPTIONS

2	AD	S	REVISED & REDRAWN
1	AD		ECR # U90658
			KBW 06-14-89 RW

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°	
3 PLACE	± .010	---	---
2 PLACE	± .014	± 0.25	---
1 PLACE	---	± 0.35	---
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
DRWG. BY	CHK'D. BY	SCALE	2 : 1
KBW	RW		
APPR'D. BY	RAS		
TITLE		REVISE ONLY ON CAD SYSTEM	
.093/(2.36) HOUSINGS			
PLUG & RECEPTACLE			
15 CIRCUIT .198/(5.03)Ø			
MOLEX	MOLEX INCORPORATED	SHEET NO.	DATE
LITSE,ILL.	60532	1 OF 2	CI/14/89
PART NO.	DRWG. NO.	SEE CHART SD-1375-*	
FILE NAME	M137515	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SIZE
S04			CP C

PLUG			RECEPTACLE	
ORDER NO	ENG NO		ORDER NO	ENG NO
03-09-2151	1375-P		03-09-1151	1375-R
03-09-2159	1375-P4		03-09-1152	1375-R1
03-09-2158	1375-P7		03-09-1154	1375-R6
03-09-7158	1375-P7BK	OBSOLETE	03-09-1157	1375-R6-1
			03-09-6154	1375-R6BK

LEGEND FOR PLUG:

1375-P***

OPTIONS: _____

BLANK = W/O EARS, W/ PULL TABS, W/O LOCK WINDOWS
 2 = W/ STANDARD EARS, W/O PULL TABS, W/O LOCK WINDOWS
 4 = W/ PREBENT EARS, W/O PULL TABS, W/ LOCK WINDOWS
 6 = W/O EARS, W/O PULL TABS, W/ LOCK WINDOWS
 7 = W/O EARS, W/ PULL TABS, W/ LOCK WINDOWS
 8 = W/ PREBENT EARS, W/O PULL TABS, W/O LOCK WINDOWS

COLOR: _____

BLANK = NATURAL COLOR
 AM = AMBER BK = BLACK BU = BLUE
 BN = BROWN GY = GRAY GN = GREEN
 OR = ORANGE RD = RED YW = YELLOW

LEGEND FOR RECEPTACLE:




1375-R***

OPTIONS: _____

BLANK = W/ PREBENT EARS, W/O LOCK RAMPS
 1 = W/O EARS, W/O LOCK RAMPS
 6 = W/ STANDARD EARS & LOCK RAMPS
 6-1 = W/O EARS, W/ LOCK RAMPS


COLOR: _____

BLANK = NATURAL COLOR
 AM = AMBER BK = BLACK BU = BLUE
 BN = BROWN GY = GRAY GN = GREEN
 OR = ORANGE RD = RED YW = YELLOW



RECOMMENDED PANEL OPENING

HOUSING	DIM. "A"	DIM. "B"	"C" PREBENT EAR	"C" STANDARD EAR	"C" SPECIAL EAR
PLUG	1.343/(34.11)	.760/(19.30)	.40/(10.2)	.36/(9.1)	---
RECEPT. W/ RAMPS	1.240/(31.50)	.725/(18.42)	.41/(10.4)	.37/(9.4)	.31/(7.8)
RECEPT. W/O RAMPS	1.240/(31.50)	.655/(16.64)	.41/(10.4)	.37/(9.4)	.31/(7.8)



DETAIL B
 .093/(2.36) PREBENT MOUNTING EAR
 (SCALE 4:1)

- NOTES
- MOLEX PRODUCT SPEC 02-09 APPLIES.
 - MATERIAL: NYLON TYPE 6/6, 94V-2.
 - ETCHED CIRCUIT I.D. NUMBERS ON SIDE OF HOUSINGS TO BE PRESENT ON PARTS FROM TOOLS BUILT AFTER 2/28/94.

LTR.	REVISIONS	LTR.	REVISIONS	LTR.	REVISIONS
		AC1	SEE SHEET I	Y1	SEE SHEET I
		AC	SEE SHEET I	Y	SEE SHEET I
		AB	SEE SHEET I	X	SEE SHEET I
		AA1	SEE SHEET I	W	SEE SHEET I
		AA	SEE SHEET I	V	SEE SHEET I
		Z	SEE SHEET I	T	SEE SHEET I
AD	SEE SHEET I	Y2	SEE SHEET I	S	SEE SHEET I

DIMENSIONS SHOWN (METRIC) INCH
 UNLESS OTHERWISE SPECIFIED
 TOLERANCES: ANGULAR ± 1/2°

INCH	METRIC
5 PLACE ± .010	---
2 PLACE ± .014 ± 0.25	---
1 PLACE --- ± 0.35	---

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DRWG. BY: KBW CHK'D. BY: RW
 APP'D. BY: RAS SCALE: - : -

REVISIONS ONLY ON CAD SYSTEM

TITLE: .093/(2.36) HOUSINGS PLUG & RECEPTACLE 15 CIRCUIT .198/(5.03)0

PART NO. SEE CHART SD-1375-*

MOLEX INCORPORATED U.S.A. SHEET NO. 2 DATE 6/14/89

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.