

Within Series Adaptor 31_SHV-50-0-1/133_N

Description

Adaptor jack/jack
SHV jack (female) / SHV jack (female)

Interface standard
Series SHV - IEC 60498_MIL-STD-348A/314



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 0.3 GHz

Mechanical Data

Number of matings 500
Weight 0.0184 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - SHV jack (female)

| Piece Parts | Material | Surface Plating |
|----------------|------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |

Interface - SHV jack (female)

| Piece Parts | Material | Surface Plating |
|----------------|------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |

Related Documents

Catalogue drawing DCA-00013821

Ordering Information

Single package 31_SHV-50-0-1/133_NE