

Within Series Adaptor 45_BNC-75-0-1/133_N

Description

T-adaptor, 1 plug, 2 jacks, asymmetric
BNC plug (male) / BNC jack (female)

Interface standard

Series BNC - Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

| | |
|--------------------------|-------|
| Impedance | 75 Ω |
| Interface frequency max. | 1 GHz |

Mechanical Data

| | |
|-------------------|-----------|
| Number of matings | 500 |
| Weight | 0.0182 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

Interface - BNC plug (male)

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |

Interface - BNC jack (female)

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |

Related Documents

| | |
|-------------------|--------------|
| Catalogue drawing | DCA-00013486 |
|-------------------|--------------|

Ordering Information

| | |
|----------------|----------------------|
| Single package | 45_BNC-75-0-1/133_NE |
|----------------|----------------------|