

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680211](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 0.34mm² TPE Cable, 0.30m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Tees and Splitters
 Series [120068](#)
 IP Rating IP67
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Type Splitter - In-line
 UPC 78678883476

Physical


Color - Cable Jacket Yellow
 Drop Connector Micro-Change (M12)
 Drop Gender Male
 Keyway Single
 LED Indicator No
 Left Trunk Connector Micro-Change (M12)
 Left Trunk Gender Female
 Leg 1 Length 0.30m
 Leg 2 Length 0.30m
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 55.538/g
 Poles 3 Female/4 Male
 Right Trunk Connector Micro-Change (M12)
 Right Trunk Gender Female
 Temperature Range - Operating -30°C to +70°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 884A31K05M003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120068 Series](#)