

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200770023](#)  
**Status:** **Active**  
**Overview:** [Brad Micro-Change \(M12\) Connectors](#)  
**Description:** [Micro-Change \(M12\) Closure Cap](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family [Field Attachable / Accessories](#)  
 Series [120077](#)  
 IP Rating [N/A](#)  
 Material - Contact [N/A](#)  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name [Micro-Change \(M12\)](#)  
 Type [Accessory - Closure Cap](#)  
 UPC [78678824048](#)

**Physical**

Cable Diameter [N/A](#)  
 Coupling Type [Internal Thread](#)  
 Diagnostics / LEDs [No](#)  
 Diagnostics Port [No](#)  
 Gender [N/A](#)  
 Keyway [N/A](#)  
 Material - Connector Body [Aluminum](#)  
 Material - Coupling Nut [N/A](#)  
 Material - Plating Mating [n/a](#)  
 Net Weight [12.110/g](#)  
 Orientation [N/A](#)  
 Poles [N/A](#)  
 Temperature Range - Operating [N/A](#)  
 Wire Size AWG [N/A](#)

**Electrical**

Current - Maximum per Contact [N/A](#)  
 Voltage - Maximum [N/A](#)

**Material Info**

Engineering Number [80011](#)

**Reference - Drawing Numbers**

Sales Drawing [SD-120077-003](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[120077 Series](#)