

PRODUCT-DETAILS

# RD2

## RD2 Residual Current Monitor



### General Information

Extended Product Type	RD2
Product ID	2CSM142120R1201
EAN	8012542058007
Catalog Description	RD2 Residual Current Monitor
Long Description	Residual current monitors (RCMs) with external transformer can detect leakage currents. Through minidip you can set sensitivity and intervention time. Operating voltage: 230...400V a.c.

### Technical

Standards	IEC EN 62020
Mounting Type	DIN-rail
Rated Operational Voltage	230 ... 400 V AC
Dimensions	2 modules
Power Loss	at Rated Operating Conditions per Pole 3.4 W

### Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

### Dimensions

Product Net Width	35 mm
Product Net Height	0.085 m
Product Net Depth / Length	65 mm
Product Net Weight	0.105 kg

---

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.041 m
Package Level 1 Height	0.08 m
Package Level 1 Depth / Length	0.103 m
Package Level 1 Gross Weight	0.15 kg
Package Level 1 EAN	8012542058007

---

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364190

---

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5627
Instructions and Manuals	0400 - 9924
RoHS Information	9AKK106713A5627

---

### Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	0400 - 9924

---

### Classifications

Object Classification Code	Q
ETIM 4	EC001445 - Residual current monitoring relay
ETIM 5	EC001445 - Residual current monitoring relay
ETIM 6	EC001445 - Residual current monitoring relay
ETIM 7	EC001445 - Residual current monitoring relay

---

### Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Monitors, RCMs

