



2-3/4-Inch Tree Climbers with Gaffs 15 to 19-Inch



Secure sleeve and leg iron connection. 2 slotted hex-head bolts with lock washers and barrel-type nuts join the steel sleeve and leg iron together. Steel split ring secures ankle strap in place and allows for quick replacement.

Specifications

Type:	Adjustable	Special Features:	Adjustable Climber Length Steel Sleeve
Overall Width:	4.438" (11.3 cm)	Material:	Steel
Adjustable Length:	15" to 19" (38.1 to 48.3 cm)	Weight:	1.6 oz (45 g)