

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2157101123](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Clik-Mate Male-to-Clik-Mate Male, Tin (Sn) Plated, 225.00mm Length, 24 AWG, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">215710</a>
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CLIK-Mate-to-CLIK-Mate
Overview	<a href="#">Off-the-Shelf Pre-Crimped Leads</a>
Product Name	CLIK-Mate
UPC	193264604982

**Physical**

Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Male-Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.797/g
Packaging Type	Bag
Plating min - Mating	0.406µm
Plating min - Termination	0.406µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.78-1.28mm
Wire Size AWG	24
Wire/Cable Type	UL 10002

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2157101121-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[215710 Series](#)

**Use With**

[CLIK-Mate Housing 502578](#) , [503149](#)