

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2147531031](#)
Status: **Active**
Overview: Micro-Fit Connector System
Description: Micro-Fit 3.0 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 3 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	214753
Application	Power, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0-to-Pigtail
Overview	<u>Micro-Fit Connector System</u>
Product Name	Micro-Fit 3.0
Type	Discrete Wire Assembly
UPC	193264586134

Physical

Cable Length	150.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	6.377/g
Number of Rows	1
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	Yes
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	18
Wire/Cable Type	Discrete Wire, UL 10002

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Sales Drawing	2147531031-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214753 Series](#)

Mates With

Micro-Fit 3.0 Receptacle Housing [43645](#)