



Combination spanner, offset, 111M/

Set of Combination spanners, offset in Metric sizes.
DIN 3113 / ISO 3318 / ISO 7738

Finish: nickel and chrome-plated, fine-polished.


Material: VANADIUM-EXTRA.

Open-end angle 15°, ring end 15° offset, equal openings at both ends, short type.
With Dynamic-Drive-Profile.

T = sets in black plastic wallet.

111M/S6 and **111M/10** in attractive sales cardboard box.

111M/S12 on a functional black plastic wall holder.



111M/7T	1828882	1	7	8 10 13 14 17 19 22	575
111M/11T	1828899	1	11	8 9 10 11 12 13 14 15 17 19 22	740
111M/14T	1828905	1	14	6 8 9 10 13 14 15 17 19 22 24 27 30 32	2270
111M/17T	1828912	1	17	6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	1615
111M/26T	1828929	1	26	6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 32	4355
111M/S6	3006097	1	6	10 11 13 16 17 18	565
111M/10	1828936	1	10	8 9 10 11 12 13 14 17 19 22	960
111M/S12	1837624	1	12	8 9 10 11 12 13 14 15 16 17 18 19	895