



# PL-Q 4 Pin

## PL-Q 28W/840/4P 1CT/10BOX

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 4-pin version is designed for operation on electronic gear.

### Product data

General Information	
Cap-Base	GR10Q [ GR10q]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	95 %
LSF Preheat 8000 h Rated	89 %
LSF Preheat 16000 h Rated	22 %
LSF Preheat 20000 h Rated	4 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	2050 lm
Luminous Flux (Rated) (Nom)	2050 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	73.2 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	86 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	80 %


LLMF 12000 h Rated	79 %
LLMF 16000 h Rated	78 %
LLMF 20000 h Rated	78 %
Operating and Electrical	
Power (Nom)	24.8 W
Lamp Current (Nom)	0.320 A
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4 Pins
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	31 kWh

# PL-Q 4 Pin

Product Data	
Full product code	871150026993525
Order product name	PL-Q 28W/840/4P 1CT/10BOX
EAN/UPC - Product	8711500269935
Order code	927939384040
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	927939384040
Net Weight (Piece)	127.000 g
ILCOS Code	FSS-28/40/1B-E-GR10q


## Dimensional drawing




PL-Q 28W/840/4P

Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 28W/840/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm

## Photometric data




LDPB\_PLQ4P\_840-Spectral power distribution B/W




LDPO\_PLQ4P\_840-Spectral power distribution Colour

## Lifetime




LDLM\_PLQ4P\_0001-Lumen maintenance diagram



LDLE\_PLQ4P\_0002-Life expectancy diagram

# PL-Q 4 Pin

## Lifetime



LDLE\_PLQ4P\_0001-Life expectancy diagram

