

## TECHNICAL DATA SHEET

Part#: 9248SL

Cutters - Medium Taper Relieved Head -★★★★- Carbon Steel - Slim Line - Black Oxide Coated

The 9248SL five star Lazer Line<sup>®</sup> medium tapered/relieved optimum flush cutter has a cutting capacity of .001" - .030" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

- |                       |   |
|-----------------------|---|
| • Precision Level     | ★★★★                                      |
| • Material            | Carbon                                    |
| • Surface Resistivity | 10 <sup>10</sup> ohms/sq                  |
| • Shape               | Taper Relieved Head                       |
| • Type of Cut         | Lazer Flush                               |
| • Group               | Cutting Tools                             |
| • Cutting Capacity    | 50 - 20 AWG / .001 - .030" / .03 - .75 mm |
| • Blade Angle         | 16°                                       |
| • Blade Length        | .278" (6.95mm)                            |
| • Body Width          | 0.375" (9.38mm)                           |
| • Body Height         | .225" (5.63mm)                            |
| • OAL                 | 4.5" (112.5mm)                            |
| • Weight (OZ)         | 3   |
| • UPC                 | 662847014093                              |
| • Schedule B          | 8203.20.60.60                             |
| • ECCN                | EAR99                                     |
| • UNSPSC Code         | 27111511                                  |
| • Country of Origin   | USA                                       |

